

Menu Route Map

NOTE

- Red color values indicate the default settings.
- The setting items or setting values with “*” may not be displayed depending on the availability of the optional accessories and other settings.

See the e-Manual for details on settings.

[Setup] Menu

Control Menu	
Sleep Mode	<div>High (Deep Sleep)</div> <div>Mid (Printer Sleep)</div>
Sleep Even if Error	<div>Off</div> <div>On</div>
Deep Sleep Eco Prior	<div>Off</div> <div>On</div>
Auto Sleep Time	<div>5 min.</div> <div>10 min.</div> <div>15 min.</div> <div>30 min.</div> <div>60 min.</div> <div>120 min.</div>
Sleep When Using USB*	<div>Do Not Allow</div> <div>Allow</div>
Timer Settings	<div>Wake Up Timer</div> <div>Wake Up Time</div> <div>Auto Reset Time</div> <div>Sleep Timer</div> <div>Sleep Time</div>
Warning Step	<div>Toner Cart. Warning</div> <div>Continue Printing</div> <div>Stop Printing</div>
Auto Skip Error	<div>Off</div> <div>On</div>
Language	<div>Čeština</div> <div>Dansk</div> <div>Deutsch</div> <div>English</div> <div>Español</div> <div>Français</div> <div>Italiano</div> <div>Magyar</div> <div>Nederlands</div> <div>Norsk</div> <div>Polski</div> <div>Português</div> <div>Русский</div> <div>Suomi</div> <div>Svenska</div>

Türkçe

中文 (简体)

한국어

Alarm

Off

On

Show Warnings

Toner Cart. Warning

Off

On

Mnt. Kit Warning

Off

On

Drawer Empty

Off

On

E-Mail Trans. Error

Off

On

Date/Time Settings

Date

01/01 2001 to 12/31 2030

12/24 Hour Clock

12 Hour (AM/PM)

24 Hour

Time

00:00:00 AM/PM to 11:59:59 AM/PM
(00:00:00 to 23:59:59)

Daylight Savings

DST Settings: Off, On

Start Date/Time: Month, Week, Day, Time

End Date/Time: Month, Week, Day, Time

Time Zone

GMT-12:00 to GMT-05:00 to GMT+12:00

Main Pwr Quick Start

Off

On

SD Card*

Off

On

Interrupt Print*

Off

On

Sec. Print Del. Time*

1 hr.

2 hr.

3 hr.

6 hr.

12 hr.

24 hr.

Secure Job Log*

Off

On

USB-Connected PC OS

Mac OS

Windows

Other

PDL Selection (PnP)

UFR II

UFR II (V4)

PCL6

PS3

XPS (Direct)

Mng. Settings

Settings Key Lock

Off

On

Sys Manager Settings

Sys Manager Password

RMT-SW

Off

On

Adjust Screen

Contrast

-3 to 0 to +3

Backlight Brightness	<div>Off</div> <div>Level 1</div> <div>Level 2</div> <div>Level 3</div>
Animated Instruction	<div>Off</div> <div>On</div>
Show Toner Gauge	<div>Off</div> <div>On</div>
Set. Comp. Notify	<div>Off</div> <div>1 sec.</div> <div>2 sec.</div> <div>3 sec.</div>
Scrolling Speed	<div>Slow</div> <div>Normal</div> <div>Fast</div>

Paper Source	
Paper Source	<div>Auto</div> <div>Envelope Tray*</div> <div>Multi-Purpose Tray</div> <div>Drawer 1</div> <div>Drawer 2*</div> <div>Drawer 3*</div> <div>Drawer 4*</div> <div>Drawer 5*</div>
Env. Tray Paper Size*	<div>Free Size</div> <div>Custom Size</div> <div>Custom Size</div> <div>Env. ISO-C5</div> <div>Env. Monarch</div> <div>Env. No.10</div> <div>Env. DL</div>
MP Tray Paper Size	<div>A6</div> <div>A5</div> <div>A5</div> <div>B5</div> <div>A4</div> <div>LTR</div> <div>LGL</div> <div>EXEC</div> <div>Free Size</div> <div>Custom Size</div> <div>Custom Size</div> <div>Env. ISO-C5</div> <div>Env. Monarch</div> <div>Env. No.10</div> <div>Env. DL</div> <div>Index Card</div> <div>STMT</div> <div>FLSC</div> <div>16K</div>
Drawer N Paper Size (N=1, 2, 3, 4, 5)*	<div>A6*</div> <div>A5*</div> <div>Free Size</div> <div>Auto*</div> <div>Custom Size*</div> <div>Custom Size*</div> <div>STMT*</div> <div>FLSC*</div> <div>16K*</div>
Standard Paper Size	<div>A6</div> <div>A5</div> <div>B5</div> <div>A4</div>

LTR

LGL

EXEC

Env. ISO-C5

Env. Monarch

Env. No.10

Env. DL

Index Card

STMT

FLSC

16K

MP Tray Priority

Off

On

MP Tray for Mix Ppr.

Off

On

Auto Select Drawer

Do Not Use

Use

Default Paper Type

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Heavy 3

Envelope

Envelope H

Labels

Env. Tray Paper Type*

Envelope

Envelope H

Mixed Types

MP Tray Paper Type

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Heavy 3

Envelope

Envelope H

Labels

Mixed Types

Drawer N Paper Type (N=1, 2, 3, 4, 5)*

Plain

Plain L

Plain L2

Heavy 1

Mixed Types

Manual 2-Sided (MP)

1st Side

2nd Side

2-Sided Printing

Off

On

Select Drawer1 Model

Standard Drawer

Custom Media Drawer

A5 Drawer

Network

TCP/IP Settings

IPv4 Settings

IPv4: Off, On

IP Mode: Auto, Manual

Protocol*

Use DHCP: Off, On

Use BOOTP: Off, On

Use RARP: Off, On

Auto IP*: Off, On

IP Address Settings

IP Address: 0.0.0.0 to 255.255.255.255

Subnet Mask: 0.0.0.0 to 255.255.255.255

Gateway Address: 0.0.0.0 to 255.255.255.255

DNS

Primary Address: 0.0.0.0 to 255.255.255.255

Secondary Address: 0.0.0.0 to 255.255.255.255

mDNS Settings*

mDNS: Off, On

mDNS Name*

DHCP Option

Acquire Host Name: Off, On

DNS Dynamic Update: Off, On

IPv6 Settings

IPv6: Off, On

mDNS Settings*

mDNS: Off, On

Use IPv4 Name (mDNS)*: Off, On

mDNS Name*

WINS Resolution

Off

On

FTP

FTP Print: Off, On

Allow Set. via FTP: Off, On

LPD Settings

LPD Print: Off, On

RX Timeout*: 1 to 60 (min.)

RAW Settings

RAW Print: Off, On

RX Timeout*: 1 to 60 (min.)

IPP Print

Off

On

WSD

WSD Print: Off, On

WSD Browsing*: Off, On

Multicast Discovery: Off, On

HTTP

Off

On

Proxy Settings

Proxy: Off, On

Server Address*

Port Number*: 1 to 80 to 65535

Same Domain*: Use Proxy, Do Not Use Proxy

Proxy Authentication*: Off, On

User Name*

Password*

SNTP

Off

On

Discovery Response

Off

On

IPSec

Off

On

Sleep Notif. Set.

Sleep Mode Notif.: Off, On

Port Number*: 1 to 11427 to 65535

Routers to Traverse*: 0 to 3 to 254

Notif. Interval*: 60 to 600 to 65535

Mopria

Off

On

Google Cloud Print

Use Cloud Print: Off, On

Registration Status

SMB*

SMB Server

Off

On

SMB Print*

Off

On

SNMP Settings

SNMPv1 Settings

SNMPv1: Off, On

Dctd. Community Set.

Dctd. Community: Off, Read/Write, Read Only

SNMPv3 Settings

SNMPv3: Off, On

User Settings N (N=1, 2, 3, 4, 5)*

Auth. Password

Encryption Password

Rjct Packet in Sleep

Off

On

Spooler*

Off

On

Receive in Parallel

Off

On

Wait Time at Startup

0 to 300 (sec.)

Remote UI Settings

Remote UI

Off

On

RUI Access Sec. Set.

Off

On

Remote UI Access PIN

TLS*

Off

On

Ethernet Driver

Auto Detect

Off

On

Communication Mode*

Half Duplex

Full Duplex

Ethernet Type*

10 Base-T

100 Base-TX

1000 Base-T

Sleep Mode Priority

Optimal Balance

Exit Speed

Energy Saving

IEEE802.1X

Off

On

Address Filter

Off

On

MAC Address

(Display only)

E-Mail Print Set.

POP3 RX Interval

0 to 90 (min.)

POP3 RX

Off

On

SMTP RX

Off

On

Init. Network Set.

Layout

Number of Copies

1 to 9999

Offset Y

-1.97 to 0.00 to +1.97 (inches)

(-50.0 to 0.0 to +50.0 (mm))

Offset X

-1.97 to 0.00 to +1.97 (inches)

(-50.0 to 0.0 to +50.0 (mm))

Binding Location

Long Edge

Short Edge

Gutter

-1.97 to 0.00 to +1.97 (inches)

(-50.0 to 0.0 to +50.0 (mm))

Alternative Method

Off

On

Print Quality

Resolution

600 dpi

1200 dpi

Image Refinement*

Off

On

Toner Save

Off

On

Density*

-8 to 0 to +8

Density (Fine Adj)*

High

-8 to 0 to +8

Mid

-8 to 0 to +8

Low

-8 to 0 to +8

Halftones

Text

Resolution

Gradation

Color Tone

High Resolution

Graphics

Resolution

Gradation

Color Tone

High Resolution

Image

Resolution

Gradation

Color Tone

High Resolution

Reduce Quality

Continue Printing

Stop Printing

Adj. Prt. Line Width

-7 to 0 to +8

Interface

Interface Selection

USB

OffOn

Network

OffOn

USB Adv. Functions

Adv. Func. Settings: Meap Priority, USB Over NW Priority

USB Storage Device

• MEAP Driver: Off, On

Timeout

Timeout

OffOn

Timeout Time*

5 to 15 to 300 (seconds)

Connection Recog.

OffOn

Extended RX Buffer

OffOn

User Maintenance

Adj. Print Position

Offset Y (Env. Tray)*

-0.20 to 0.00 to +0.20 (in.)
(-5.0 to 0.0 to +5.0 (mm))

Offset X (Env. Tray)*

-0.20 to 0.00 to +0.20 (in.)
(-5.0 to 0.0 to +5.0 (mm))

Offset Y (MP Tray)

-0.20 to 0.00 to +0.20 (inches)
(-5.0 to 0.0 to +5.0 (mm))

Offset X (MP Tray)

-0.20 to 0.00 to +0.20 (inches)
(-5.0 to 0.0 to +5.0 (mm))

Offset Y (Drawer 1 to 5)*

-0.20 to 0.00 to +0.20 (inches)
(-5.0 to 0.0 to +5.0 (mm))

Offset X (Drawer 1 to 5)*

-0.20 to 0.00 to +0.20 (in.)
(-5.0 to 0.0 to +5.0 (mm))

Offset Y (2-Sided)*

-0.20 to 0.00 to +0.20 (in.)
(-5.0 to 0.0 to +5.0 (mm))

Offset X (2-Sided)*

-0.20 to 0.00 to +0.20 (in.)
(-5.0 to 0.0 to +5.0 (mm))

Recovery Printing

OffOn

Initialize Counter

Fixing Unit

Check Paper Size

OffOn

Substitute Size

OffOn

Short Edge Fd. Prty.

OffOn

Sp. Transfer Mode

OffOn

Special Print Mode A

Off

Mode 1

Mode 2

Mode 3

Mode 4

Special Density Mode

OffOn

SD Card Maintenance*

Format

Completely Del. Data

Special Print Adj. C

OffOn

Barcode Adj. Mode

Off

Mode 1

Mode 2

Mode 3

Mode 4

Update Firmware

USB

Network

Paper Feed Method

Multi-Purpose Tray

Speed Priority

Print Side Priority

Drawer 1 to 5*

Speed Priority

Print Side Priority

Show Job List

OffOn

Import/Export Set.

IMPORT

EXPORT

Notify to Clean

OffOn

Clean. Notif. Timing*

1000 to 50000 (pages)

Toner Check Timing

DefaultCustom

Spec Tnr Chk Timing

1 to 20 to 99 (%)

Print Mode

Auto Mode Selection

Auto Selection

PCL

PS

PDF

XPS

Auto Select

PCL

OffOn

PS

OffOn

PDF

OffOn

XPS

OffOn

Mode Priority

None

PCL

PS

PDF

XPS

UFR II

Paper Save

OffOn

PCL

Paper Save

Off

On

Orientation

Portrait

Landscape

Font Number

0 to 104

Point Size*

4.00 to 12.00 to 999.75 point

Pitch*

0.44 to 10.00 to 99.99 cpi

Form Lines

5 to 60 to 128 lines

Character Code

PC8

ROMAN8

ROMAN9

ISOL1

ISOL2

ISOL5

ISOL6

ISOL9

PC775

PC8DN

PC850

PC852

PC858

PC8TK

PC1004

WINL1

WINL2

WINL5

WINBALT

DESKTOP

PSTEXT

LEGAL

ISO4

ISO6

ISO11

ISO15

ISO17

ISO21

ISO60

ISO69

WIN 30

MCTEXT

PC864

ARABIC8

WINARB

PC866

ISOCYR

WINCYR

PC851

GREEK8

ISOGRK

PC8GRK

WINGRK

PC862

HEBREW7

HEBREW8

ISOHEB

Custom Size

Do Not Set

Set

Unit of Measurement*

Millimeters

Inches

3

X Dimension*

3.00 to **8.50 in.** (76.2 to **215.9 mm**)

Y Dimension*

5.00 to **14.00 in.** (127.0 to **355.6 mm**)

Append CR to LF

Yes

No

Enlarge A4 Prt Width

Off

On

BarDIMM*

Enable

Disable

FreeScape*

Off

~

"

#

\$

/

\

?

{

}

|

Imaging

Image Orientation

Auto

Vertical

Horizontal

Zoom

Off

Auto

Print Position

Auto

Center

Top Left

TIFF Spooler

Off

On

Show Warnings

Off

Print

Panel

Print E-Mail Text

Off

On

Limit E-Mail Print*

Off

On

Enlarge Print Area

Off

On

Halftones

Resolution

Gradation

High Resolution

Grayscale Conversion

sRGB

NTSC

Uniform RGB

XPS

Halftones

Text

Resolution

Gradation

High Resolution

Graphics

Resolution

Gradation

High Resolution

Image

Resolution

Gradation

High Resolution

Grayscale Conversion

Text

sRGB

NTSC

Uniform RGB

Graphics

sRGB

NTSC

Uniform RGB

Image

sRGB

NTSC

Uniform RGB

Compressed Img Mode*

Image Priority

Output Priority

Compressed Img Outpt

Output

Display Error

PDF

Fit to Paper Size

Off

On

Enlarge Print Area

Off

On

N on 1

Off

2 on 1

4 on 1

6 on 1

8 on 1

9 on 1

16 on 1

Comment Print

Off

Auto

Halftones

Text

Resolution

Gradation

High Resolution

Graphics

Resolution

Gradation

High Resolution

Image

Resolution

Gradation

High Resolution

Grayscale Conversion

sRGB

NTSC

Uniform RGB

PS

Job Timeout

0 to 3600 seconds

Print PS Errors

Off

On

Halftones

Text

Resolution

Gradation

High Resolution

Graphics

Resolution

Gradation

High Resolution

Image

Resolution

Gradation

High Resolution

Grayscale Conversion

sRGB

NTSC

Uniform RGB

MEAP Settings

Select Def. Screen

Print Screen

MEAP

Check Counter

101: Total 1

(Display only)

Initialize Menu

[Utility] Menu

Check Counter

101: Total 1

(Display only)

Configuration Page

Network Status Print

Consmb. Status Prt.

IPSec Policy List

PCL Utility

Font List

PS Utility

Configuration Page

Font List

Cleaning

A4

LTR

E-Mail Print Utility

Received E-Mail

E-Mail RX Log List

Printing Pos. Print

Page Count List

Counter Report

Print MEAP Sys. Info

Serial Number

(Display only)

Consumables Info.

Paper Information

Envelope Tray*: (Display only)

Multi-Purpose Tray: (Display only)

Drawer 1: (Display only)

Drawer 2*: (Display only)

Drawer 3*: (Display only)

Drawer 4*: (Display only)

Drawer 5*: (Display only)

Toner Cart. Model

(Display only)

Remaining Toner

(Display only)

[Job] Menu

Encrypted Print*

Secured Print*

Stored Job List*

Stored Job Print*

Job Print Log*

Stored Job Print Log*

Report Print Log*

E-Mail Print Log*

[Reset] Menu

Soft Reset (Hard Reset)

Form Feed

Shut Down

[Select Feeder] Menu

Paper Source

Auto

Envelope Tray*

Multi-Purpose Tray

Drawer 1

Drawer 2*

Drawer 3*

Drawer 4*

Drawer 5*

Env. Tray Paper Size*

Free Size

Custom Size

Custom Size

Env. ISO-C5

Env. Monarch

Env. No.10

Env. DL

MP Tray Paper Size

A6

A5

A5

B5

A4

LTR

LGL

EXEC

Free Size

Custom Size

Custom Size

Env. ISO-C5

Env. Monarch

Env. No.10

Env. DL

Index Card

STMT

FLSC

16K

Drawer N Paper Size (N=1, 2, 3, 4, 5)*

A6*

A5*

Free Size

Auto*

Custom Size*

Custom Size*

STMT*

FLSC*

16K*

Standard Paper Size

A6

A5

B5

A4

LTR

LGL

EXEC

Env. ISO-C5

Env. Monarch

Env. No.10

Env. DL

Index Card

STMT

FLSC

16K

MP Tray Priority

Off

On

MP Tray for Mix Ppr.

Off

On

Auto Select Drawer

Do Not Use

Use

Default Paper Type

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Heavy 3

Envelope

Envelope H

Labels

Env. Tray Paper Type*

Envelope

Envelope H

Mixed Types

MP Tray Paper Type

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Heavy 3

Envelope

Envelope H

Labels

Mixed Types

Drawer N Paper Type (N=1, 2, 3, 4, 5)*

Plain

Plain L

Plain L2

Heavy 1

Mixed Types

Manual 2-Sided (MP)

1st Side

2nd Side

2-Sided Printing

Off

On

Select Drawer1 Model

Standard Drawer

Custom Media Drawer

A5 Drawer